

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255383

Luminaire Tested: P3AS20R309035D010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309035D010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2196.1 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255383
CATALOG NUMBER: P3AS20R309035D010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1255383
 CATALOG NUMBER: P3AS20R309035D010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	93	92	90
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	93	91	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	90	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	88	85	83	82
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	86	83	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	84	81	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	82	79	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	80	77	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1747207
5°	1724429
10°	1505583
15°	956964
20°	379153
25°	126636
30°	58920
35°	26689
40°	10248
45°	5024
50°	1467
55°	650
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5024 cd/sqm



TEST NUMBER: P1255383
 CATALOG NUMBER: P3AS20R309035D010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	716.2	32.6
10°-20°	1110.7	50.6
20°-30°	286.4	13.0
30°-40°	67.3	3.1
40°-50°	13.1	0.6
50°-60°	1.5	0.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2113.4	96.2
0°-40°	2180.6	99.3
0°-60°	2195.3	100.0
0°-90°	2196.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2196.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7968	
5°	7834	716
15°	4215	1111
25°	523	286
35°	100	67
45°	16	13
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1255383
CATALOG NUMBER: P3AS20R309035D010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7967.9
1°	7961.9
2°	7943.2
3°	7921.9
4°	7890.3
5°	7834.1
6°	7742.8
7°	7591.1
8°	7384.0
9°	7113.7
10°	6761.7
11°	6343.1
12°	5886.2
13°	5360.2
14°	4809.5
15°	4215.4
16°	3633.2
17°	3072.2
18°	2534.3
19°	2040.8
20°	1624.8
21°	1278.7
22°	1005.9
23°	796.2
24°	637.6
25°	523.4
26°	436.5
27°	370.8
28°	320.5
29°	274.5
30°	232.7
32.5°	146.6
35°	99.7
37.5°	62.2
40°	35.8
42.5°	23.9
45°	16.2
47.5°	9.4
50°	4.3
52.5°	1.7
55°	1.7
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9



TEST NUMBER: P1255383
CATALOG NUMBER: P3AS20R309035D010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)