

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256142

Luminaire Tested: P3AS02R259040DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259040DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 334.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256142

CATALOG NUMBER: P3AS02R259040DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1256142

CATALOG NUMBER: P3AS02R259040DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	110	113	111	109	108	107	106	105		103	103	102		100
2	112	108	105	103	110	107	104	102	104	102	100		101	99	98		98
3	108	104	101	98	107	103	100	97	100	98	96		98	96	94		96
4	105	100	97	94	104	99	96	93	97	95	92		96	93	91		94
5	103	97	93	90	101	96	93	90	95	92	89		93	91	89		92
6	100	94	90	87	99	93	90	87	92	89	87		91	88	86		90
7	97	91	88	85	96	91	87	85	90	87	84		89	86	84		88
8	95	89	85	83	94	89	85	82	88	84	82		87	84	82		86
9	93	87	83	80	92	86	83	80	86	82	80		85	82	80		84
10	91	85	81	78	90	84	81	78	84	80	78		83	80	78		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	357099
5°	331190
10°	256842
15°	128786
20°	42307
25°	16815
30°	6305
35°	1820
40°	830
45°	310
50°	273
55°	191
60°	219
65°	259
70°	192
75°	254
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 379 cd/sqm

TEST NUMBER: P1256142

CATALOG NUMBER: P3AS02R259040DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.3	39.6
10°-20°	157.9	47.3
20°-30°	35.6	10.7
30°-40°	5.8	1.7
40°-50°	1.0	0.3
50°-60°	0.5	0.2
60°-70°	0.5	0.1
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.8	97.6
0°-40°	331.6	99.3
0°-60°	333.2	99.8
0°-90°	334.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	334.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1628	
5°	1505	132
15°	567	158
25°	70	36
35°	7	6
45°	1	1
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256142

CATALOG NUMBER: P3AS02R259040DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1628.5
1°	1625.9
2°	1612.7
3°	1588.6
4°	1552.1
5°	1504.6
6°	1447.9
7°	1386.5
8°	1316.2
9°	1239.3
10°	1153.5
11°	1054.6
12°	940.7
13°	821.6
14°	693.8
15°	567.3
17.5°	323.3
20°	181.3
22.5°	109.4
25°	69.5
27.5°	42.8
30°	24.9
32.5°	13.1
35°	6.8
37.5°	4.5
40°	2.9
42.5°	1.8
45°	1.0
47.5°	0.8
50°	0.8
52.5°	0.8
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1256142
CATALOG NUMBER: P3AS02R259040DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)