

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256152

Luminaire Tested: P3AS02R259040DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1256152  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R259040DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 134.0 lumens  
Efficiency: N/A  
Efficacy: 37.2 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1256152  
CATALOG NUMBER: P3AS02R259040DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1256152

CATALOG NUMBER: P3AS02R259040DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	85958
5°	80189
10°	64238
15°	43610
20°	26392
25°	15436
30°	8786
35°	4845
40°	2576
45°	1364
50°	785
55°	573
60°	526
65°	519
70°	513
75°	424
80°	379
85°	252

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1364 cd/sqm



TEST NUMBER: P1256152  
 CATALOG NUMBER: P3AS02R259040DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.3	24.1
10°-20°	52.8	39.4
20°-30°	30.2	22.5
30°-40°	11.9	8.9
40°-50°	3.7	2.7
50°-60°	1.4	1.1
60°-70°	1.0	0.7
70°-80°	0.5	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.3	86.0
0°-40°	127.2	94.9
0°-60°	132.3	98.7
0°-90°	134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	134.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	392	
5°	364	32
15°	192	53
25°	64	30
35°	18	12
45°	4	4
55°	2	1
65°	1	1
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P1256152  
CATALOG NUMBER: P3AS02R259040DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	392.0
1°	391.2
2°	388.0
3°	382.4
4°	374.6
5°	364.3
6°	352.3
7°	338.7
8°	323.0
9°	306.8
10°	288.5
11°	270.5
12°	250.6
13°	231.0
14°	210.9
15°	192.1
17.5°	148.9
20°	113.1
22.5°	84.9
25°	63.8
27.5°	47.3
30°	34.7
32.5°	25.1
35°	18.1
37.5°	12.8
40°	9.0
42.5°	6.1
45°	4.4
47.5°	3.1
50°	2.3
52.5°	1.8
55°	1.5
57.5°	1.4
60°	1.2
62.5°	1.0
65°	1.0
67.5°	0.9
70°	0.8
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.3
85°	0.1
87.5°	0.1



TEST NUMBER: P1256152  
CATALOG NUMBER: P3AS02R259040DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)