

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256205

Luminaire Tested: P3AS02R359040DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256205
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359040DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 333.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256205

CATALOG NUMBER: P3AS02R359040DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1256205

CATALOG NUMBER: P3AS02R359040DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217132
5°	212722
10°	197881
15°	145086
20°	74300
25°	26784
30°	10432
35°	3641
40°	1489
45°	403
50°	341
55°	382
60°	351
65°	259
70°	321
75°	424
80°	379
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 504 cd/sqm

TEST NUMBER: P1256205

CATALOG NUMBER: P3AS02R359040DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	27.1
10°-20°	169.0	50.8
20°-30°	59.9	18.0
30°-40°	10.5	3.1
40°-50°	1.5	0.5
50°-60°	0.8	0.2
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	319.0	95.8
0°-40°	329.5	98.9
0°-60°	331.8	99.6
0°-90°	333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	333.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	990	
5°	966	90
15°	639	169
25°	111	60
35°	14	10
45°	1	2
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256205

CATALOG NUMBER: P3AS02R359040DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	990.2
1°	990.0
2°	986.8
3°	980.8
4°	975.3
5°	966.4
6°	957.2
7°	947.0
8°	934.4
9°	914.7
10°	888.7
11°	852.8
12°	809.5
13°	758.1
14°	701.5
15°	639.1
17.5°	476.0
20°	318.4
22.5°	192.0
25°	110.7
27.5°	66.1
30°	41.2
32.5°	23.9
35°	13.6
37.5°	8.7
40°	5.2
42.5°	2.6
45°	1.3
47.5°	1.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0



TEST NUMBER: P1256205

CATALOG NUMBER: P3AS02R359040DE010 E3CB1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)