

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255444

Luminaire Tested: P3AS20R409035D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255444
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409035D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2435.0 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255444

CATALOG NUMBER: P3AS20R409035D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1255444

CATALOG NUMBER: P3AS20R409035D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1241172
5°	1232222
10°	1199956
15°	1071902
20°	710748
25°	266265
30°	71226
35°	27840
40°	10019
45°	4745
50°	1467
55°	650
60°	395
65°	467
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4745 cd/sqm

TEST NUMBER: P1255444

CATALOG NUMBER: P3AS20R409035D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.3	21.7
10°-20°	1251.1	51.4
20°-30°	567.4	23.3
30°-40°	73.5	3.0
40°-50°	12.7	0.5
50°-60°	1.5	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2346.7	96.4
0°-40°	2420.2	99.4
0°-60°	2434.5	100.0
0°-90°	2435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5660	
5°	5598	528
15°	4722	1251
25°	1100	567
35°	104	74
45°	15	13
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1255444

CATALOG NUMBER: P3AS20R409035D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5660.2
1°	5656.8
2°	5648.3
3°	5635.5
4°	5619.3
5°	5598.0
6°	5573.3
7°	5542.6
8°	5505.1
9°	5453.9
10°	5389.1
11°	5313.3
12°	5211.8
13°	5086.5
14°	4922.9
15°	4721.7
16°	4465.1
17°	4172.7
18°	3821.5
19°	3450.7
20°	3045.8
21°	2640.9
22°	2241.9
23°	1844.7
24°	1454.3
25°	1100.5
26°	814.9
27°	596.7
28°	448.4
29°	348.6
30°	281.3
31°	232.7
32°	194.4
32.5°	177.3
33°	160.3
34°	130.4
35°	104.0
36°	81.8
37°	64.8
37.5°	58.0
38°	51.1
39°	42.6
40°	35.0
42.5°	23.0
45°	15.3



TEST NUMBER: P1255444
CATALOG NUMBER: P3AS20R409035D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	9.4
50°	4.3
52.5°	1.7
55°	1.7
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)