

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256240

Luminaire Tested: P3AS02R409040DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409040DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 367.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256240

CATALOG NUMBER: P3AS02R409040DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1256240

CATALOG NUMBER: P3AS02R409040DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	187068
5°	185714
10°	180847
15°	161545
20°	107133
25°	40139
30°	10736
35°	4203
40°	1517
45°	713
50°	205
55°	115
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1256240

CATALOG NUMBER: P3AS02R409040DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.6	21.7
10°-20°	188.6	51.4
20°-30°	85.5	23.3
30°-40°	11.1	3.0
40°-50°	1.9	0.5
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.7	96.4
0°-40°	364.8	99.4
0°-60°	366.9	100.0
0°-90°	367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	853	
5°	844	80
15°	712	189
25°	166	86
35°	16	11
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1256240

CATALOG NUMBER: P3AS02R409040DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	853.1
1°	852.6
2°	851.3
3°	849.4
4°	846.9
5°	843.7
6°	840.0
7°	835.4
8°	829.7
9°	822.0
10°	812.2
11°	800.8
12°	785.5
13°	766.6
14°	742.0
15°	711.6
16°	673.0
17°	628.9
18°	576.0
19°	520.1
20°	459.1
21°	398.0
22°	337.9
23°	278.0
24°	219.2
25°	165.9
26°	122.8
27°	89.9
28°	67.6
29°	52.5
30°	42.4
31°	35.1
32°	29.3
32.5°	26.7
33°	24.2
34°	19.7
35°	15.7
36°	12.3
37°	9.8
37.5°	8.7
38°	7.7
39°	6.4
40°	5.3
42.5°	3.5
45°	2.3



TEST NUMBER: P1256240

CATALOG NUMBER: P3AS02R409040DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.4
50°	0.6
52.5°	0.3
55°	0.3
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)