

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256261

Luminaire Tested: P3AS02R409040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 193.0 lumens
Efficiency: N/A
Efficacy: 53.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256261

CATALOG NUMBER: P3AS02R409040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256261

CATALOG NUMBER: P3AS02R409040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60105
5°	58882
10°	54820
15°	47787
20°	38503
25°	28865
30°	20282
35°	13304
40°	8044
45°	4807
50°	2866
55°	2294
60°	2061
65°	1764
70°	1667
75°	1356
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4807 cd/sqm

TEST NUMBER: P1256261

CATALOG NUMBER: P3AS02R409040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	12.9
10°-20°	58.0	30.0
20°-30°	54.6	28.3
30°-40°	31.6	16.4
40°-50°	12.6	6.5
50°-60°	5.5	2.9
60°-70°	3.4	1.8
70°-80°	1.8	0.9
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	137.4	71.2
0°-40°	169.0	87.6
0°-60°	187.2	97.0
0°-90°	193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	193.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	268	25
15°	210	58
25°	119	55
35°	50	32
45°	16	13
55°	6	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1256261

CATALOG NUMBER: P3AS02R409040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.1
2.5°	272.5
5°	267.5
7.5°	258.3
10°	246.2
12.5°	229.9
15°	210.5
17.5°	188.7
20°	165.0
22.5°	141.4
25°	119.3
27.5°	98.8
30°	80.1
32.5°	63.9
35°	49.7
37.5°	37.6
40°	28.1
42.5°	21.0
45°	15.5
47.5°	11.3
50°	8.4
52.5°	6.8
55°	6.0
57.5°	5.5
60°	4.7
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.6
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.1
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)