

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255485

Luminaire Tested: P3AS20R459035D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459035D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255485

CATALOG NUMBER: P3AS20R459035D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255485

CATALOG NUMBER: P3AS20R459035D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183187
5°	179000
10°	165127
15°	143588
20°	117960
25°	91771
30°	67783
35°	47703
40°	29770
45°	16126
50°	8733
55°	7493
60°	6710
65°	5759
70°	4937
75°	5083
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16126 cd/sqm

TEST NUMBER: P1255485

CATALOG NUMBER: P3AS20R459035D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.3	12.2
10°-20°	174.9	28.4
20°-30°	173.6	28.2
30°-40°	111.8	18.2
40°-50°	43.1	7.0
50°-60°	17.5	2.8
60°-70°	11.1	1.8
70°-80°	6.0	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	68.9
0°-40°	535.6	87.1
0°-60°	596.1	96.9
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	835	
5°	813	75
15°	632	175
25°	379	174
35°	178	112
45°	52	43
55°	20	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1255485

CATALOG NUMBER: P3AS20R459035D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	835.4
2.5°	831.1
5°	813.2
7.5°	782.5
10°	741.6
12.5°	690.5
15°	632.5
17.5°	569.4
20°	505.5
22.5°	440.7
25°	379.3
27.5°	321.4
30°	267.7
32.5°	220.8
35°	178.2
37.5°	139.8
40°	104.0
42.5°	75.0
45°	52.0
47.5°	34.9
50°	25.6
52.5°	21.3
55°	19.6
57.5°	17.0
60°	15.3
62.5°	12.8
65°	11.1
67.5°	9.4
70°	7.7
72.5°	6.8
75°	6.0
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)