

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255495

Luminaire Tested: P3AS20R509035D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509035D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2381.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255495

CATALOG NUMBER: P3AS20R509035D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1255495

CATALOG NUMBER: P3AS20R509035D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	829232
5°	814394
10°	781972
15°	717053
20°	632295
25°	484625
30°	263509
35°	84778
40°	19923
45°	2698
50°	2388
55°	2676
60°	2281
65°	2698
70°	2244
75°	2965
80°	2147
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 4277 cd/sqm

TEST NUMBER: P1255495

CATALOG NUMBER: P3AS20R509035D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	347.2	14.6
10°-20°	878.0	36.9
20°-30°	879.3	36.9
30°-40°	247.2	10.4
40°-50°	14.9	0.6
50°-60°	5.7	0.2
60°-70°	4.5	0.2
70°-80°	3.0	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2104.5	88.4
0°-40°	2351.7	98.8
0°-60°	2372.3	99.6
0°-90°	2381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2381.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3782	
5°	3700	347
15°	3159	878
25°	2003	879
35°	317	247
45°	9	15
55°	7	6
65°	5	5
75°	4	3
85°	2	1
90°	0	

TEST NUMBER: P1255495

CATALOG NUMBER: P3AS20R509035D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3781.6
2.5°	3762.5
5°	3699.8
7.5°	3614.5
10°	3511.9
12.5°	3357.0
15°	3158.6
17.5°	2930.6
20°	2709.6
22.5°	2434.6
25°	2003.0
27.5°	1491.4
30°	1040.7
32.5°	628.2
35°	316.7
37.5°	149.7
40°	69.6
42.5°	26.1
45°	8.7
47.5°	7.0
50°	7.0
52.5°	7.0
55°	7.0
57.5°	5.2
60°	5.2
62.5°	5.2
65°	5.2
67.5°	3.5
70°	3.5
72.5°	3.5
75°	3.5
77.5°	1.7
80°	1.7
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)