

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256344

Luminaire Tested: P3AS02R559040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 191.0 lumens
Efficiency: N/A
Efficacy: 53.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256344

CATALOG NUMBER: P3AS02R559040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256344

CATALOG NUMBER: P3AS02R559040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		79
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		73
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		67
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		55
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		52
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51948
5°	50649
10°	47093
15°	41930
20°	35633
25°	28768
30°	21927
35°	15606
40°	10276
45°	6109
50°	3582
55°	2217
60°	1974
65°	1764
70°	1539
75°	1356
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6109 cd/sqm

TEST NUMBER: P1256344

CATALOG NUMBER: P3AS02R559040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.4	11.2
10°-20°	51.2	26.8
20°-30°	54.2	28.4
30°-40°	36.7	19.2
40°-50°	16.1	8.4
50°-60°	5.7	3.0
60°-70°	3.4	1.8
70°-80°	1.8	0.9
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	126.8	66.4
0°-40°	163.5	85.6
0°-60°	185.3	97.0
0°-90°	191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	237	
5°	230	21
15°	185	51
25°	119	54
35°	58	37
45°	20	16
55°	6	6
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1256344

CATALOG NUMBER: P3AS02R559040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	236.9
2.5°	235.1
5°	230.1
7.5°	222.0
10°	211.5
12.5°	198.9
15°	184.7
17.5°	169.0
20°	152.7
22.5°	135.7
25°	118.9
27.5°	102.3
30°	86.6
32.5°	71.6
35°	58.3
37.5°	46.2
40°	35.9
42.5°	27.0
45°	19.7
47.5°	14.4
50°	10.5
52.5°	7.3
55°	5.8
57.5°	5.2
60°	4.5
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)