

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256367

Luminaire Tested: P3AS02R609040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 216.0 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256367

CATALOG NUMBER: P3AS02R609040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256367

CATALOG NUMBER: P3AS02R609040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38352
5°	37904
10°	36606
15°	34575
20°	31876
25°	28865
30°	25624
35°	21897
40°	17404
45°	12280
50°	7335
55°	3708
60°	3552
65°	3269
70°	3013
75°	2881
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12280 cd/sqm

TEST NUMBER: P1256367

CATALOG NUMBER: P3AS02R609040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.2	7.5
10°-20°	42.6	19.7
20°-30°	54.7	25.3
30°-40°	50.7	23.5
40°-50°	30.9	14.3
50°-60°	10.3	4.8
60°-70°	6.3	2.9
70°-80°	3.5	1.6
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	113.4	52.5
0°-40°	164.1	76.0
0°-60°	205.2	95.0
0°-90°	216.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	216.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	175	
5°	172	16
15°	152	43
25°	119	55
35°	82	51
45°	40	31
55°	10	10
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1256367

CATALOG NUMBER: P3AS02R609040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	174.9
2.5°	174.1
5°	172.2
7.5°	168.8
10°	164.4
12.5°	158.9
15°	152.3
17.5°	144.7
20°	136.6
22.5°	127.9
25°	119.3
27.5°	110.4
30°	101.2
32.5°	92.0
35°	81.8
37.5°	71.0
40°	60.8
42.5°	50.1
45°	39.6
47.5°	30.7
50°	21.5
52.5°	12.8
55°	9.7
57.5°	8.9
60°	8.1
62.5°	7.1
65°	6.3
67.5°	5.5
70°	4.7
72.5°	3.9
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)