

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255518

Luminaire Tested: P3AS20R509035D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509035D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1957.0 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255518
CATALOG NUMBER: P3AS20R509035D010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1255518
 CATALOG NUMBER: P3AS20R509035D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	623064
5°	610520
10°	571866
15°	511944
20°	430817
25°	328809
30°	213678
35°	126699
40°	73223
45°	36686
50°	13646
55°	10628
60°	9911
65°	9028
70°	8912
75°	8811
80°	8840
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36686 cd/sqm



TEST NUMBER: P1255518
 CATALOG NUMBER: P3AS20R509035D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.0	13.2
10°-20°	623.6	31.9
20°-30°	611.8	31.3
30°-40°	308.2	15.7
40°-50°	97.4	5.0
50°-60°	25.2	1.3
60°-70°	17.9	0.9
70°-80°	11.0	0.6
80°-90°	3.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1493.5	76.3
0°-40°	1801.7	92.1
0°-60°	1924.4	98.3
0°-90°	1957.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1957.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2841	
5°	2774	258
15°	2255	624
25°	1359	612
35°	473	308
45°	118	97
55°	28	25
65°	17	18
75°	10	11
85°	4	4
90°	0	



TEST NUMBER: P1255518
CATALOG NUMBER: P3AS20R509035D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2841.4
2.5°	2824.0
5°	2773.6
7.5°	2683.1
10°	2568.3
12.5°	2420.4
15°	2255.1
17.5°	2063.7
20°	1846.2
22.5°	1611.3
25°	1359.0
27.5°	1091.0
30°	843.9
32.5°	635.1
35°	473.3
37.5°	349.7
40°	255.8
42.5°	181.0
45°	118.3
47.5°	67.9
50°	40.0
52.5°	29.6
55°	27.8
57.5°	24.4
60°	22.6
62.5°	20.9
65°	17.4
67.5°	15.7
70°	13.9
72.5°	12.2
75°	10.4
77.5°	8.7
80°	7.0
82.5°	5.2
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)