

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256385

Luminaire Tested: P3AS02R659040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 129.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256385

CATALOG NUMBER: P3AS02R659040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256385

CATALOG NUMBER: P3AS02R659040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30414
5°	30046
10°	28924
15°	27083
20°	24362
25°	20687
30°	16180
35°	11538
40°	7557
45°	4652
50°	2354
55°	841
60°	746
65°	726
70°	641
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4652 cd/sqm

TEST NUMBER: P1256385

CATALOG NUMBER: P3AS02R659040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.8	9.9
10°-20°	33.2	25.7
20°-30°	38.8	30.1
30°-40°	27.1	21.0
40°-50°	11.9	9.3
50°-60°	2.7	2.1
60°-70°	1.3	1.0
70°-80°	0.8	0.6
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	84.8	65.8
0°-40°	112.0	86.8
0°-60°	126.5	98.1
0°-90°	129.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	129.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	139	
5°	136	13
15°	119	33
25°	86	39
35°	43	27
45°	15	12
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256385

CATALOG NUMBER: P3AS02R659040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	138.7
2.5°	138.2
5°	136.5
7.5°	133.7
10°	129.9
12.5°	125.1
15°	119.3
17.5°	112.2
20°	104.4
22.5°	95.5
25°	85.5
27.5°	75.0
30°	63.9
32.5°	53.2
35°	43.1
37.5°	34.2
40°	26.4
42.5°	19.9
45°	15.0
47.5°	11.1
50°	6.9
52.5°	3.6
55°	2.2
57.5°	1.9
60°	1.7
62.5°	1.5
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.6
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)