

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255577

Luminaire Tested: P3AS20R609035D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609035D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1265.0 lumens
Efficiency: N/A
Efficacy: 43.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255577

CATALOG NUMBER: P3AS20R609035D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255577

CATALOG NUMBER: P3AS20R609035D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	320588
5°	313404
10°	293404
15°	263225
20°	226353
25°	187172
30°	147896
35°	109834
40°	75627
45°	47447
50°	26097
55°	15292
60°	13727
65°	11726
70°	10002
75°	10336
80°	8840
85°	8806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 47447 cd/sqm

TEST NUMBER: P1255577

CATALOG NUMBER: P3AS20R609035D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.5	10.5
10°-20°	322.0	25.5
20°-30°	353.2	27.9
30°-40°	257.3	20.3
40°-50°	121.6	9.6
50°-60°	39.8	3.1
60°-70°	22.5	1.8
70°-80°	12.2	1.0
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.8	63.9
0°-40°	1065.1	84.2
0°-60°	1226.5	97.0
0°-90°	1265.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1265.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1462	
5°	1424	133
15°	1160	322
25°	774	353
35°	410	257
45°	153	122
55°	40	40
65°	23	23
75°	12	12
85°	4	4
90°	0	

TEST NUMBER: P1255577

CATALOG NUMBER: P3AS20R609035D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1462.0
2.5°	1453.3
5°	1423.8
7.5°	1378.6
10°	1317.7
12.5°	1244.7
15°	1159.5
17.5°	1067.4
20°	970.0
22.5°	870.9
25°	773.6
27.5°	676.2
30°	584.1
32.5°	495.4
35°	410.3
37.5°	333.8
40°	264.2
42.5°	203.4
45°	153.0
47.5°	111.3
50°	76.5
52.5°	50.4
55°	40.0
57.5°	34.8
60°	31.3
62.5°	26.1
65°	22.6
67.5°	19.1
70°	15.6
72.5°	13.9
75°	12.2
77.5°	8.7
80°	7.0
82.5°	5.2
85°	3.5
87.5°	1.7
90°	0.0

(END OF REPORT)