

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256402

Luminaire Tested: P3AS02R659040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 181.9 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256402

CATALOG NUMBER: P3AS02R659040DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1256402

CATALOG NUMBER: P3AS02R659040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46268
5°	45102
10°	42017
15°	37639
20°	32506
25°	27050
30°	21320
35°	15794
40°	10878
45°	6760
50°	3684
55°	2294
60°	1974
65°	1764
70°	1539
75°	1356
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6760 cd/sqm

TEST NUMBER: P1256402

CATALOG NUMBER: P3AS02R659040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.0	10.5
10°-20°	46.1	25.3
20°-30°	51.0	28.0
30°-40°	37.0	20.3
40°-50°	17.3	9.5
50°-60°	5.8	3.2
60°-70°	3.4	1.9
70°-80°	1.8	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.1	63.8
0°-40°	153.1	84.1
0°-60°	176.2	96.9
0°-90°	181.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	181.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	211	
5°	205	19
15°	166	46
25°	112	51
35°	59	37
45°	22	17
55°	6	6
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1256402

CATALOG NUMBER: P3AS02R659040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	211.0
2.5°	209.7
5°	204.9
7.5°	197.8
10°	188.7
12.5°	177.9
15°	165.8
17.5°	152.7
20°	139.3
22.5°	125.4
25°	111.8
27.5°	97.9
30°	84.2
32.5°	71.1
35°	59.0
37.5°	48.0
40°	38.0
42.5°	29.1
45°	21.8
47.5°	15.7
50°	10.8
52.5°	7.3
55°	6.0
57.5°	5.2
60°	4.5
62.5°	3.9
65°	3.4
67.5°	2.9
70°	2.4
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)