

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255589

Luminaire Tested: P3AS20R659035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255589
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 855.1 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255589

CATALOG NUMBER: P3AS20R659035D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255589

CATALOG NUMBER: P3AS20R659035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201629
5°	199207
10°	191646
15°	179524
20°	161481
25°	137113
30°	107232
35°	76426
40°	50008
45°	30918
50°	15692
55°	5543
60°	4868
65°	4877
70°	4360
75°	4321
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30918 cd/sqm

TEST NUMBER: P1255589

CATALOG NUMBER: P3AS20R659035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	9.9
10°-20°	220.1	25.7
20°-30°	257.2	30.1
30°-40°	179.8	21.0
40°-50°	79.1	9.3
50°-60°	17.6	2.1
60°-70°	9.0	1.0
70°-80°	5.4	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.3	65.8
0°-40°	742.0	86.8
0°-60°	838.8	98.1
0°-90°	855.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	905	85
15°	791	220
25°	567	257
35°	286	180
45°	100	79
55°	14	18
65°	9	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1255589

CATALOG NUMBER: P3AS20R659035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	919.5
2.5°	916.1
5°	905.0
7.5°	886.3
10°	860.7
12.5°	829.2
15°	790.8
17.5°	744.0
20°	692.0
22.5°	633.2
25°	566.7
27.5°	496.8
30°	423.5
32.5°	352.8
35°	285.5
37.5°	226.7
40°	174.7
42.5°	132.1
45°	99.7
47.5°	73.3
50°	46.0
52.5°	23.9
55°	14.5
57.5°	12.8
60°	11.1
62.5°	10.2
65°	9.4
67.5°	7.7
70°	6.8
72.5°	6.0
75°	5.1
77.5°	4.3
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)