

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256420

Luminaire Tested: P3AS02R709040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 92.0 lumens
Efficiency: N/A
Efficacy: 25.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256420

CATALOG NUMBER: P3AS02R709040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256420

CATALOG NUMBER: P3AS02R709040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21577
5°	21175
10°	19973
15°	18139
20°	15868
25°	13380
30°	10964
35°	8486
40°	6069
45°	3845
50°	1910
55°	1185
60°	1009
65°	934
70°	833
75°	763
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3845 cd/sqm

TEST NUMBER: P1256420

CATALOG NUMBER: P3AS02R709040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.0	9.8
10°-20°	22.2	24.2
20°-30°	25.3	27.5
30°-40°	19.8	21.5
40°-50°	9.7	10.6
50°-60°	3.0	3.3
60°-70°	1.8	1.9
70°-80°	0.9	1.0
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	56.5	61.4
0°-40°	76.3	82.9
0°-60°	89.0	96.7
0°-90°	92.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	92.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	98	
5°	96	9
15°	80	22
25°	55	25
35°	32	20
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256420

CATALOG NUMBER: P3AS02R709040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	98.4
2.5°	97.9
5°	96.2
7.5°	93.5
10°	89.7
12.5°	85.2
15°	79.9
17.5°	74.1
20°	68.0
22.5°	61.6
25°	55.3
27.5°	49.1
30°	43.3
32.5°	37.4
35°	31.7
37.5°	26.4
40°	21.2
42.5°	16.5
45°	12.4
47.5°	8.7
50°	5.6
52.5°	3.7
55°	3.1
57.5°	2.7
60°	2.3
62.5°	2.0
65°	1.8
67.5°	1.5
70°	1.3
72.5°	1.0
75°	0.9
77.5°	0.8
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)