

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255624

Luminaire Tested: P3AS20R709035D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255624
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709035D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255624
CATALOG NUMBER: P3AS20R709035D010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1255624

CATALOG NUMBER: P3AS20R709035D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71	71	71	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65	65	65	65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49	49	49	49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	143782
5°	141140
10°	133086
15°	120795
20°	105663
25°	89134
30°	72973
35°	56617
40°	40504
45°	25646
50°	12793
55°	7837
60°	6710
65°	6174
70°	5450
75°	5083
80°	4293
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25646 cd/sqm



TEST NUMBER: P1255624
 CATALOG NUMBER: P3AS20R709035D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	9.8
10°-20°	148.1	24.2
20°-30°	168.6	27.5
30°-40°	131.9	21.5
40°-50°	64.8	10.6
50°-60°	19.9	3.2
60°-70°	11.8	1.9
70°-80°	6.3	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.5	61.4
0°-40°	508.4	82.9
0°-60°	593.0	96.7
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	656	
5°	641	60
15°	532	148
25°	368	169
35°	212	132
45°	83	65
55°	20	20
65°	12	12
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1255624
CATALOG NUMBER: P3AS20R709035D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	655.7
2.5°	652.3
5°	641.2
7.5°	623.3
10°	597.7
12.5°	567.9
15°	532.1
17.5°	493.7
20°	452.8
22.5°	410.1
25°	368.4
27.5°	327.4
30°	288.2
32.5°	249.0
35°	211.5
37.5°	175.7
40°	141.5
42.5°	110.0
45°	82.7
47.5°	58.0
50°	37.5
52.5°	24.7
55°	20.5
57.5°	17.9
60°	15.3
62.5°	13.6
65°	11.9
67.5°	10.2
70°	8.5
72.5°	6.8
75°	6.0
77.5°	5.1
80°	3.4
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)