

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256538

Luminaire Tested: P3AS05R209040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 208.0 lumens
Efficiency: N/A
Efficacy: 28.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256538

CATALOG NUMBER: P3AS05R209040DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256538

CATALOG NUMBER: P3AS05R209040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51443
5°	50077
10°	46069
15°	40545
20°	34770
25°	29203
30°	23624
35°	17962
40°	12795
45°	8435
50°	5219
55°	3441
60°	3114
65°	2854
70°	2693
75°	2457
80°	2273
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8435 cd/sqm

TEST NUMBER: P1256538

CATALOG NUMBER: P3AS05R209040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	10.1
10°-20°	49.7	23.9
20°-30°	55.2	26.5
30°-40°	42.1	20.3
40°-50°	21.5	10.4
50°-60°	8.9	4.3
60°-70°	5.5	2.6
70°-80°	3.1	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	126.0	60.6
0°-40°	168.1	80.8
0°-60°	198.5	95.4
0°-90°	208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	208.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	235	
5°	228	21
15°	179	50
25°	121	55
35°	67	42
45°	27	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256538

CATALOG NUMBER: P3AS05R209040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	234.6
1°	234.9
2°	233.8
3°	232.5
4°	230.4
5°	227.5
6°	224.1
7°	220.4
8°	216.4
9°	211.6
10°	206.9
12.5°	193.1
15°	178.6
17.5°	163.8
20°	149.0
22.5°	134.2
25°	120.7
27.5°	107.3
30°	93.3
32.5°	80.1
35°	67.1
37.5°	55.8
40°	44.7
42.5°	35.1
45°	27.2
47.5°	20.6
50°	15.3
52.5°	11.4
55°	9.0
57.5°	8.2
60°	7.1
62.5°	6.3
65°	5.5
67.5°	4.8
70°	4.2
72.5°	3.4
75°	2.9
77.5°	2.4
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.3
90°	0.0

(END OF REPORT)