

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255701

Luminaire Tested: P3AS24R259035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255701
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R259035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1047.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255701
CATALOG NUMBER: P3AS24R259035D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1255701
 CATALOG NUMBER: P3AS24R259035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	82	78	76	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	671613
5°	626611
10°	501950
15°	340728
20°	206168
25°	120563
30°	68669
35°	37771
40°	20038
45°	10544
50°	6141
55°	4588
60°	3947
65°	4151
70°	3847
75°	3389
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10544 cd/sqm



TEST NUMBER: P1255701
 CATALOG NUMBER: P3AS24R259035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	24.1
10°-20°	412.6	39.4
20°-30°	235.8	22.5
30°-40°	93.0	8.9
40°-50°	28.5	2.7
50°-60°	11.3	1.1
60°-70°	7.6	0.7
70°-80°	4.2	0.4
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	901.0	86.1
0°-40°	994.1	94.9
0°-60°	1033.8	98.7
0°-90°	1047.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1047.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3063	
5°	2847	253
15°	1501	413
25°	498	236
35°	141	93
45°	34	29
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1255701
CATALOG NUMBER: P3AS24R259035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3062.8
1°	3056.8
2°	3031.8
3°	2987.7
4°	2926.7
5°	2846.7
6°	2752.6
7°	2646.5
8°	2523.5
9°	2397.4
10°	2254.3
11°	2113.2
12°	1958.1
13°	1805.1
14°	1648.0
15°	1500.9
17.5°	1163.7
20°	883.5
22.5°	663.4
25°	498.3
27.5°	369.2
30°	271.2
32.5°	196.1
35°	141.1
37.5°	100.1
40°	70.0
42.5°	48.0
45°	34.0
47.5°	24.0
50°	18.0
52.5°	14.0
55°	12.0
57.5°	11.0
60°	9.0
62.5°	8.0
65°	8.0
67.5°	7.0
70°	6.0
72.5°	5.0
75°	4.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	1.0



TEST NUMBER: P1255701
CATALOG NUMBER: P3AS24R259035D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)