

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256571

Luminaire Tested: P3AS05R259040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 168.9 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256571

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256571

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61355
5°	58860
10°	51569
15°	41453
20°	31853
25°	24098
30°	17420
35°	11564
40°	7013
45°	4093
50°	2593
55°	2103
60°	1842
65°	1660
70°	1346
75°	1356
80°	1010
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4093 cd/sqm

TEST NUMBER: P1256571

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.3	14.4
10°-20°	50.5	29.9
20°-30°	45.7	27.0
30°-40°	27.4	16.2
40°-50°	10.9	6.4
50°-60°	5.0	3.0
60°-70°	3.1	1.8
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.5	71.3
0°-40°	147.9	87.6
0°-60°	163.8	97.0
0°-90°	168.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	168.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	267	24
15°	183	50
25°	100	46
35°	43	27
45°	13	11
55°	6	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1256571

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	279.8
1°	279.8
2°	278.5
3°	275.6
4°	271.9
5°	267.4
6°	261.6
7°	255.0
8°	247.4
9°	239.8
10°	231.6
11°	222.1
12°	212.4
13°	202.6
14°	192.9
15°	182.6
17.5°	158.3
20°	136.5
22.5°	116.7
25°	99.6
27.5°	83.5
30°	68.8
32.5°	55.3
35°	43.2
37.5°	32.9
40°	24.5
42.5°	17.9
45°	13.2
47.5°	10.0
50°	7.6
52.5°	6.3
55°	5.5
57.5°	4.7
60°	4.2
62.5°	3.4
65°	3.2
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.3
80°	0.8
82.5°	0.5
85°	0.5
87.5°	0.3



TEST NUMBER: P1256571

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)