

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256576

Luminaire Tested: P3AS05R259040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R25 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 345.0 lumens
Efficiency: N/A
Efficacy: 47.9 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256576

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256576

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125253
5°	120163
10°	105275
15°	84609
20°	65012
25°	49188
30°	35550
35°	23610
40°	14313
45°	8342
50°	5322
55°	4320
60°	3772
65°	3373
70°	2757
75°	2711
80°	2020
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8342 cd/sqm

TEST NUMBER: P1256576

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	14.4
10°-20°	103.1	29.9
20°-30°	93.2	27.0
30°-40°	56.0	16.2
40°-50°	22.2	6.4
50°-60°	10.3	3.0
60°-70°	6.3	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.0	71.3
0°-40°	302.0	87.5
0°-60°	334.5	96.9
0°-90°	345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	345.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	546	50
15°	373	103
25°	203	93
35°	88	56
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256576

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	571.2
1°	571.2
2°	568.5
3°	562.6
4°	555.1
5°	545.9
6°	534.1
7°	520.6
8°	505.0
9°	489.4
10°	472.8
11°	453.4
12°	433.5
13°	413.6
14°	393.7
15°	372.7
17.5°	323.3
20°	278.6
22.5°	238.3
25°	203.3
27.5°	170.5
30°	140.4
32.5°	112.9
35°	88.2
37.5°	67.2
40°	50.0
42.5°	36.6
45°	26.9
47.5°	20.4
50°	15.6
52.5°	12.9
55°	11.3
57.5°	9.7
60°	8.6
62.5°	7.0
65°	6.5
67.5°	5.4
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.7
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5



TEST NUMBER: P1256576

CATALOG NUMBER: P3AS05R259040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)