

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255715

Luminaire Tested: P3AS24R259035D010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255715  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R259035D010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1309.0 lumens  
Efficiency: N/A  
Efficacy: 45.5 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255715

CATALOG NUMBER: P3AS24R259035D010 E3DLP1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1255715

CATALOG NUMBER: P3AS24R259035D010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 |  | 100 | 99  | 98  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 77  | 73  | 81  | 76  | 73  |  | 79  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 65  | 60  | 79  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 61  | 57  | 65  | 60  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 475247 |
| 5°  | 455931 |
| 10° | 399414 |
| 15° | 321046 |
| 20° | 246678 |
| 25° | 186640 |
| 30° | 134856 |
| 35° | 89597  |
| 40° | 54330  |
| 45° | 31631  |
| 50° | 20195  |
| 55° | 16401  |
| 60° | 14341  |
| 65° | 12712  |
| 70° | 10450  |
| 75° | 10336  |
| 80° | 7703   |
| 85° | 10315  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31631 cd/sqm

TEST NUMBER: P1255715

CATALOG NUMBER: P3AS24R259035D010 E3DLP1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 188.6  | 14.4      |
| 10°-20°   | 391.1  | 29.9      |
| 20°-30°   | 353.7  | 27.0      |
| 30°-40°   | 212.4  | 16.2      |
| 40°-50°   | 84.4   | 6.4       |
| 50°-60°   | 38.9   | 3.0       |
| 60°-70°   | 23.7   | 1.8       |
| 70°-80°   | 12.6   | 1.0       |
| 80°-90°   | 3.6    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 933.3  | 71.3      |
| 0°-40°    | 1145.7 | 87.5      |
| 0°-60°    | 1269.0 | 96.9      |
| 0°-90°    | 1309.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1309.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2167 |      |
| 5°  | 2071 | 189  |
| 15° | 1414 | 391  |
| 25° | 771  | 354  |
| 35° | 335  | 212  |
| 45° | 102  | 84   |
| 55° | 43   | 39   |
| 65° | 24   | 24   |
| 75° | 12   | 13   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1255715

CATALOG NUMBER: P3AS24R259035D010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2167.3 |
| 1°    | 2167.3 |
| 2°    | 2157.1 |
| 3°    | 2134.6 |
| 4°    | 2106.0 |
| 5°    | 2071.3 |
| 6°    | 2026.5 |
| 7°    | 1975.4 |
| 8°    | 1916.3 |
| 9°    | 1857.1 |
| 10°   | 1793.8 |
| 11°   | 1720.3 |
| 12°   | 1644.8 |
| 13°   | 1569.3 |
| 14°   | 1493.8 |
| 15°   | 1414.2 |
| 17.5° | 1226.5 |
| 20°   | 1057.1 |
| 22.5° | 904.0  |
| 25°   | 771.4  |
| 27.5° | 646.9  |
| 30°   | 532.6  |
| 32.5° | 428.6  |
| 35°   | 334.7  |
| 37.5° | 255.1  |
| 40°   | 189.8  |
| 42.5° | 138.8  |
| 45°   | 102.0  |
| 47.5° | 77.5   |
| 50°   | 59.2   |
| 52.5° | 49.0   |
| 55°   | 42.9   |
| 57.5° | 36.7   |
| 60°   | 32.7   |
| 62.5° | 26.5   |
| 65°   | 24.5   |
| 67.5° | 20.4   |
| 70°   | 16.3   |
| 72.5° | 14.3   |
| 75°   | 12.2   |
| 77.5° | 10.2   |
| 80°   | 6.1    |
| 82.5° | 4.1    |
| 85°   | 4.1    |
| 87.5° | 2.0    |



TEST NUMBER: P1255715  
CATALOG NUMBER: P3AS24R259035D010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)