

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255722

Luminaire Tested: P3AS24R309035D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R309035D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2597.0 lumens
Efficiency: N/A
Efficacy: 90.2 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255722
CATALOG NUMBER: P3AS24R309035D010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1255722
 CATALOG NUMBER: P3AS24R309035D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	91	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2114831
5°	2074857
10°	1836795
15°	1163707
20°	441738
25°	130798
30°	51654
35°	15847
40°	7013
45°	2543
50°	2081
55°	1567
60°	1798
65°	2127
70°	1282
75°	1694
80°	2526
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2543 cd/sqm



TEST NUMBER: P1255722
 CATALOG NUMBER: P3AS24R309035D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	866.5	33.4
10°-20°	1350.4	52.0
20°-30°	313.6	12.1
30°-40°	48.6	1.9
40°-50°	8.3	0.3
50°-60°	3.9	0.1
60°-70°	3.3	0.1
70°-80°	2.1	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2530.5	97.4
0°-40°	2579.1	99.3
0°-60°	2591.3	99.8
0°-90°	2597.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2597.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9644	
5°	9426	867
15°	5126	1350
25°	541	314
35°	59	49
45°	8	8
55°	4	4
65°	4	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1255722
CATALOG NUMBER: P3AS24R309035D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	9644.4
1°	9638.3
2°	9611.8
3°	9566.9
4°	9509.8
5°	9426.1
6°	9322.1
7°	9167.1
8°	8954.9
9°	8642.8
10°	8249.2
11°	7741.2
12°	7168.0
13°	6531.6
14°	5831.9
15°	5126.1
17.5°	3353.5
20°	1893.0
22.5°	966.9
25°	540.6
27.5°	332.5
30°	204.0
32.5°	110.2
35°	59.2
37.5°	38.8
40°	24.5
42.5°	14.3
45°	8.2
47.5°	6.1
50°	6.1
52.5°	4.1
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1255722
CATALOG NUMBER: P3AS24R309035D010 E3CB1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)