

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256616

Luminaire Tested: P3AS05R359040DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256616
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359040DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 684.0 lumens
Efficiency: N/A
Efficacy: 95.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256616

CATALOG NUMBER: P3AS05R359040DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1256616

CATALOG NUMBER: P3AS05R359040DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	446017
5°	436935
10°	406472
15°	298004
20°	152590
25°	54995
30°	21421
35°	7495
40°	3092
45°	837
50°	751
55°	841
60°	702
65°	571
70°	705
75°	932
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 932 cd/sqm

TEST NUMBER: P1256616

CATALOG NUMBER: P3AS05R359040DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.0	27.1
10°-20°	347.2	50.8
20°-30°	122.9	18.0
30°-40°	21.5	3.1
40°-50°	3.2	0.5
50°-60°	1.8	0.3
60°-70°	1.3	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.2	95.8
0°-40°	676.7	98.9
0°-60°	681.6	99.6
0°-90°	684.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2034	
5°	1985	185
15°	1313	347
25°	227	123
35°	28	22
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1256616

CATALOG NUMBER: P3AS05R359040DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2034.0
1°	2033.4
2°	2027.0
3°	2014.6
4°	2003.3
5°	1985.0
6°	1966.1
7°	1945.1
8°	1919.2
9°	1878.8
10°	1825.5
11°	1751.7
12°	1662.8
13°	1557.3
14°	1440.9
15°	1312.7
17.5°	977.7
20°	653.9
22.5°	394.3
25°	227.3
27.5°	135.7
30°	84.6
32.5°	49.0
35°	28.0
37.5°	17.8
40°	10.8
42.5°	5.4
45°	2.7
47.5°	2.2
50°	2.2
52.5°	2.2
55°	2.2
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1256616
CATALOG NUMBER: P3AS05R359040DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)