

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255786

Luminaire Tested: P3AS24R409035D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R409035D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2866.9 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255786

CATALOG NUMBER: P3AS24R409035D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1255786

CATALOG NUMBER: P3AS24R409035D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85		
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82		
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79		
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76		
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73		
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1509550
5°	1502285
10°	1453324
15°	1285819
20°	838930
25°	297187
30°	63022
35°	20746
40°	7586
45°	2543
50°	2081
55°	2332
60°	1798
65°	2127
70°	1282
75°	1694
80°	2526
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 3360 cd/sqm

TEST NUMBER: P1255786

CATALOG NUMBER: P3AS24R409035D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	642.2	22.4
10°-20°	1495.5	52.2
20°-30°	649.0	22.6
30°-40°	59.8	2.1
40°-50°	8.5	0.3
50°-60°	5.2	0.2
60°-70°	3.8	0.1
70°-80°	2.1	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2786.7	97.2
0°-40°	2846.5	99.3
0°-60°	2860.2	99.8
0°-90°	2866.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2866.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6884	
5°	6825	642
15°	5664	1496
25°	1228	649
35°	78	60
45°	8	8
55°	6	5
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1255786

CATALOG NUMBER: P3AS24R409035D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6884.1
2.5°	6875.9
5°	6824.9
7.5°	6716.8
10°	6527.0
12.5°	6206.7
15°	5664.0
17.5°	4764.2
20°	3595.1
22.5°	2334.1
25°	1228.3
27.5°	528.4
30°	248.9
32.5°	134.7
35°	77.5
37.5°	46.9
40°	26.5
42.5°	14.3
45°	8.2
47.5°	6.1
50°	6.1
52.5°	6.1
55°	6.1
57.5°	6.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	4.1
70°	2.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)