

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255793

Luminaire Tested: P3AS24R409035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R409035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1165.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255793

CATALOG NUMBER: P3AS24R409035D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255793

CATALOG NUMBER: P3AS24R409035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	91	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86
5	96	88	83	79	94	88	83	79	86	82	78		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	68	84	76	71	67	75	70	67		74	70	67		73
9	82	73	68	64	81	73	68	64	72	67	64		71	67	64		70
10	78	70	65	62	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	515507
5°	500527
10°	454211
15°	375235
20°	270667
25°	167429
30°	90647
35°	46846
40°	25476
45°	14265
50°	7164
55°	5352
60°	4824
65°	4670
70°	4488
75°	4236
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14265 cd/sqm

TEST NUMBER: P1255793

CATALOG NUMBER: P3AS24R409035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.6	18.0
10°-20°	450.1	38.6
20°-30°	321.2	27.6
30°-40°	118.3	10.2
40°-50°	37.2	3.2
50°-60°	12.9	1.1
60°-70°	8.9	0.8
70°-80°	5.3	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	980.9	84.2
0°-40°	1099.2	94.3
0°-60°	1149.3	98.7
0°-90°	1165.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1165.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2351	
5°	2274	210
15°	1653	450
25°	692	321
35°	175	118
45°	46	37
55°	14	13
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1255793

CATALOG NUMBER: P3AS24R409035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2350.9
2.5°	2332.9
5°	2273.9
7.5°	2175.9
10°	2039.9
12.5°	1866.9
15°	1652.9
17.5°	1412.9
20°	1159.9
22.5°	911.0
25°	692.0
27.5°	508.0
30°	358.0
32.5°	251.0
35°	175.0
37.5°	124.0
40°	89.0
42.5°	64.0
45°	46.0
47.5°	31.0
50°	21.0
52.5°	15.0
55°	14.0
57.5°	13.0
60°	11.0
62.5°	10.0
65°	9.0
67.5°	8.0
70°	7.0
72.5°	6.0
75°	5.0
77.5°	4.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)