

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256660

Luminaire Tested: P3AS05R409040DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256660
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409040DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 481.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256660
CATALOG NUMBER: P3AS05R409040DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1256660
 CATALOG NUMBER: P3AS05R409040DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107974
5°	106009
10°	99931
15°	90761
20°	79737
25°	68085
30°	56414
35°	43500
40°	30972
45°	20870
50°	11394
55°	8028
60°	7543
65°	7005
70°	6219
75°	5931
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20870 cd/sqm



TEST NUMBER: P1256660
 CATALOG NUMBER: P3AS05R409040DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	9.3
10°-20°	111.4	23.2
20°-30°	128.8	26.8
30°-40°	101.5	21.1
40°-50°	52.1	10.8
50°-60°	19.9	4.1
60°-70°	13.2	2.7
70°-80°	7.2	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.0	59.3
0°-40°	386.5	80.4
0°-60°	458.5	95.3
0°-90°	481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	481.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	492	
5°	482	45
15°	400	111
25°	281	129
35°	162	101
45°	67	52
55°	21	20
65°	14	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1256660
CATALOG NUMBER: P3AS05R409040DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	492.4
2.5°	489.7
5°	481.6
7.5°	467.6
10°	448.8
12.5°	426.7
15°	399.8
17.5°	371.9
20°	341.7
22.5°	311.0
25°	281.4
27.5°	251.9
30°	222.8
32.5°	193.2
35°	162.5
37.5°	134.0
40°	108.2
42.5°	86.1
45°	67.3
47.5°	49.0
50°	33.4
52.5°	24.2
55°	21.0
57.5°	18.8
60°	17.2
62.5°	15.1
65°	13.5
67.5°	11.3
70°	9.7
72.5°	8.1
75°	7.0
77.5°	5.4
80°	3.8
82.5°	3.2
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)