

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256676

Luminaire Tested: P3AS05R459040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 295.0 lumens
Efficiency: N/A
Efficacy: 41.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256676

CATALOG NUMBER: P3AS05R459040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256676

CATALOG NUMBER: P3AS05R459040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110781
5°	108188
10°	99441
15°	84268
20°	65386
25°	45704
30°	28789
35°	16945
40°	9589
45°	4652
50°	1603
55°	1300
60°	1272
65°	1245
70°	1154
75°	1101
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4652 cd/sqm

TEST NUMBER: P1256676

CATALOG NUMBER: P3AS05R459040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	15.4
10°-20°	101.9	34.6
20°-30°	86.6	29.3
30°-40°	41.3	14.0
40°-50°	12.4	4.2
50°-60°	3.1	1.1
60°-70°	2.3	0.8
70°-80°	1.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.0	79.3
0°-40°	275.3	93.3
0°-60°	290.8	98.6
0°-90°	295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	295.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	505	
5°	492	45
15°	371	102
25°	189	87
35°	63	41
45°	15	12
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256676

CATALOG NUMBER: P3AS05R459040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	505.2
2.5°	502.0
5°	491.5
7.5°	473.3
10°	446.6
12.5°	411.3
15°	371.2
17.5°	326.6
20°	280.2
22.5°	233.0
25°	188.9
27.5°	148.8
30°	113.7
32.5°	85.5
35°	63.3
37.5°	46.7
40°	33.5
42.5°	23.2
45°	15.0
47.5°	8.4
50°	4.7
52.5°	3.7
55°	3.4
57.5°	3.2
60°	2.9
62.5°	2.6
65°	2.4
67.5°	2.1
70°	1.8
72.5°	1.6
75°	1.3
77.5°	1.1
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)