

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256691

Luminaire Tested: P3AS05R459040DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256691
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459040DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 388.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256691

CATALOG NUMBER: P3AS05R459040DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1256691

CATALOG NUMBER: P3AS05R459040DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115561
5°	112943
10°	104184
15°	90579
20°	74416
25°	57899
30°	42766
35°	30089
40°	18778
45°	10172
50°	5492
55°	4741
60°	4254
65°	3632
70°	3077
75°	3219
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10172 cd/sqm

TEST NUMBER: P1256691

CATALOG NUMBER: P3AS05R459040DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.5	12.2
10°-20°	110.3	28.4
20°-30°	109.5	28.2
30°-40°	70.5	18.2
40°-50°	27.1	7.0
50°-60°	11.1	2.8
60°-70°	7.0	1.8
70°-80°	3.8	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.3	68.9
0°-40°	337.9	87.1
0°-60°	376.1	96.9
0°-90°	388.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	388.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	527	
5°	513	48
15°	399	110
25°	239	110
35°	112	71
45°	33	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1256691

CATALOG NUMBER: P3AS05R459040DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	527.0
2.5°	524.4
5°	513.1
7.5°	493.7
10°	467.9
12.5°	435.6
15°	399.0
17.5°	359.2
20°	318.9
22.5°	278.0
25°	239.3
27.5°	202.7
30°	168.9
32.5°	139.3
35°	112.4
37.5°	88.2
40°	65.6
42.5°	47.3
45°	32.8
47.5°	22.0
50°	16.1
52.5°	13.4
55°	12.4
57.5°	10.8
60°	9.7
62.5°	8.1
65°	7.0
67.5°	5.9
70°	4.8
72.5°	4.3
75°	3.8
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)