

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255921

Luminaire Tested: P3AS24R609035D010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R609035D010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2146.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255921

CATALOG NUMBER: P3AS24R609035D010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1255921

CATALOG NUMBER: P3AS24R609035D010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	506736
5°	501936
10°	487299
15°	456552
20°	404098
25°	338052
30°	264927
35°	192203
40°	127868
45°	79698
50°	43154
55°	12463
60°	11622
65°	10585
70°	10450
75°	10336
80°	10355
85°	10315

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 79698 cd/sqm

TEST NUMBER: P1255921

CATALOG NUMBER: P3AS24R609035D010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.7	10.0
10°-20°	558.0	26.0
20°-30°	636.0	29.6
30°-40°	451.0	21.0
40°-50°	204.6	9.5
50°-60°	43.4	2.0
60°-70°	20.9	1.0
70°-80°	12.9	0.6
80°-90°	4.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1408.7	65.6
0°-40°	1859.7	86.7
0°-60°	2107.7	98.2
0°-90°	2146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2311	
5°	2280	215
15°	2011	558
25°	1397	636
35°	718	451
45°	257	205
55°	33	43
65°	20	21
75°	12	13
85°	4	4
90°	0	

TEST NUMBER: P1255921

CATALOG NUMBER: P3AS24R609035D010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2310.9
2.5°	2302.8
5°	2280.3
7.5°	2241.6
10°	2188.5
12.5°	2113.1
15°	2011.1
17.5°	1882.6
20°	1731.7
22.5°	1568.5
25°	1397.2
27.5°	1221.7
30°	1046.3
32.5°	879.1
35°	718.0
37.5°	575.2
40°	446.7
42.5°	338.6
45°	257.0
47.5°	191.7
50°	126.5
52.5°	59.1
55°	32.6
57.5°	28.6
60°	26.5
62.5°	24.5
65°	20.4
67.5°	18.4
70°	16.3
72.5°	14.3
75°	12.2
77.5°	10.2
80°	8.2
82.5°	6.1
85°	4.1
87.5°	2.0
90°	0.0

(END OF REPORT)