

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256708

Luminaire Tested: P3AS05R509040DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509040DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 606.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256708
CATALOG NUMBER: P3AS05R509040DE010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1256708

CATALOG NUMBER: P3AS05R509040DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82	82	82	82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76	76	76	76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67	67	67	67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64	64	64	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57	57	57	57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54	54	54	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192945
5°	189060
10°	177084
15°	158525
20°	133408
25°	101812
30°	66162
35°	39244
40°	22671
45°	11350
50°	4230
55°	3288
60°	3070
65°	2802
70°	2757
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11350 cd/sqm



TEST NUMBER: P1256708
 CATALOG NUMBER: P3AS05R509040DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.9	13.2
10°-20°	193.1	31.9
20°-30°	189.4	31.3
30°-40°	95.5	15.8
40°-50°	30.1	5.0
50°-60°	7.8	1.3
60°-70°	5.5	0.9
70°-80°	3.4	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.5	76.3
0°-40°	557.9	92.1
0°-60°	595.9	98.3
0°-90°	606.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	606.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	880	
5°	859	80
15°	698	193
25°	421	189
35°	147	95
45°	37	30
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1256708
CATALOG NUMBER: P3AS05R509040DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	879.9
2.5°	874.5
5°	858.9
7.5°	830.8
10°	795.3
12.5°	749.5
15°	698.3
17.5°	639.0
20°	571.7
22.5°	498.9
25°	420.8
27.5°	337.8
30°	261.3
32.5°	196.7
35°	146.6
37.5°	108.3
40°	79.2
42.5°	56.0
45°	36.6
47.5°	21.0
50°	12.4
52.5°	9.2
55°	8.6
57.5°	7.5
60°	7.0
62.5°	6.5
65°	5.4
67.5°	4.8
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.7
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)