

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256711

Luminaire Tested: P3AS05R509040DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509040DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 4000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256711

CATALOG NUMBER: P3AS05R509040DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256711

CATALOG NUMBER: P3AS05R509040DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46948
5°	46247
10°	44199
15°	40931
20°	36800
25°	32349
30°	27498
35°	22299
40°	16746
45°	10792
50°	5117
55°	4014
60°	3815
65°	3580
70°	3206
75°	2881
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10792 cd/sqm

TEST NUMBER: P1256711

CATALOG NUMBER: P3AS05R509040DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.7	8.5
10°-20°	50.3	21.8
20°-30°	61.1	26.5
30°-40°	51.8	22.4
40°-50°	26.9	11.7
50°-60°	9.7	4.2
60°-70°	6.7	2.9
70°-80°	3.6	1.6
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	131.1	56.7
0°-40°	182.9	79.2
0°-60°	219.5	95.0
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	214	
5°	210	20
15°	180	50
25°	134	61
35°	83	52
45°	35	27
55°	10	10
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1256711

CATALOG NUMBER: P3AS05R509040DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	214.1
2.5°	213.3
5°	210.1
7.5°	205.4
10°	198.5
12.5°	189.8
15°	180.3
17.5°	169.5
20°	157.7
22.5°	145.5
25°	133.7
27.5°	121.3
30°	108.6
32.5°	96.0
35°	83.3
37.5°	70.9
40°	58.5
42.5°	46.7
45°	34.8
47.5°	23.2
50°	15.0
52.5°	11.6
55°	10.5
57.5°	9.5
60°	8.7
62.5°	7.6
65°	6.9
67.5°	5.8
70°	5.0
72.5°	4.2
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)