

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255946

Luminaire Tested: P3AS24R659035D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255946
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R659035D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 693.0 lumens
Efficiency: N/A
Efficacy: 24.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255946

CATALOG NUMBER: P3AS24R659035D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255946

CATALOG NUMBER: P3AS24R659035D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176148
5°	171758
10°	159961
15°	143361
20°	123794
25°	102974
30°	81202
35°	60177
40°	41478
45°	25708
50°	13987
55°	8793
60°	7456
65°	6745
70°	5770
75°	5083
80°	5051
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25708 cd/sqm

TEST NUMBER: P1255946

CATALOG NUMBER: P3AS24R659035D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.5	10.5
10°-20°	175.5	25.3
20°-30°	194.0	28.0
30°-40°	140.9	20.3
40°-50°	66.0	9.5
50°-60°	22.2	3.2
60°-70°	12.9	1.9
70°-80°	6.7	1.0
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	442.0	63.8
0°-40°	583.0	84.1
0°-60°	671.3	96.9
0°-90°	693.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	693.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	803	
5°	780	73
15°	632	175
25°	426	194
35°	225	141
45°	83	66
55°	23	22
65°	13	13
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1255946

CATALOG NUMBER: P3AS24R659035D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	803.3
2.5°	798.3
5°	780.3
7.5°	753.3
10°	718.4
12.5°	677.4
15°	631.5
17.5°	581.5
20°	530.5
22.5°	477.6
25°	425.6
27.5°	372.7
30°	320.7
32.5°	270.8
35°	224.8
37.5°	182.8
40°	144.9
42.5°	110.9
45°	82.9
47.5°	59.9
50°	41.0
52.5°	28.0
55°	23.0
57.5°	20.0
60°	17.0
62.5°	15.0
65°	13.0
67.5°	11.0
70°	9.0
72.5°	8.0
75°	6.0
77.5°	5.0
80°	4.0
82.5°	3.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)