

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255954

Luminaire Tested: P3AS24R709035D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R709035D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2552.0 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255954
CATALOG NUMBER: P3AS24R709035D010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1255954
 CATALOG NUMBER: P3AS24R709035D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	506758
5°	483556
10°	460067
15°	447766
20°	431237
25°	408120
30°	379603
35°	318875
40°	205528
45°	95514
50°	25040
55°	6232
60°	6271
65°	5292
70°	5257
75°	5168
80°	5177
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 95514 cd/sqm



TEST NUMBER: P1255954
 CATALOG NUMBER: P3AS24R709035D010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.6	8.1
10°-20°	554.2	21.7
20°-30°	774.3	30.3
30°-40°	718.0	28.1
40°-50°	257.4	10.1
50°-60°	21.8	0.9
60°-70°	10.8	0.4
70°-80°	7.0	0.3
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1534.2	60.1
0°-40°	2252.2	88.3
0°-60°	2531.4	99.2
0°-90°	2552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2311	
5°	2197	206
15°	1972	554
25°	1687	774
35°	1191	718
45°	308	257
55°	16	22
65°	10	11
75°	6	7
85°	2	3
90°	0	



TEST NUMBER: P1255954
CATALOG NUMBER: P3AS24R709035D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	2311.0
2.5°	2276.3
5°	2196.8
7.5°	2123.3
10°	2066.2
12.5°	2019.3
15°	1972.4
17.5°	1915.3
20°	1848.0
22.5°	1770.5
25°	1686.8
27.5°	1601.2
30°	1499.2
32.5°	1368.7
35°	1191.2
37.5°	964.8
40°	718.0
42.5°	489.5
45°	308.0
47.5°	171.3
50°	73.4
52.5°	24.5
55°	16.3
57.5°	14.3
60°	14.3
62.5°	12.2
65°	10.2
67.5°	10.2
70°	8.2
72.5°	8.2
75°	6.1
77.5°	6.1
80°	4.1
82.5°	4.1
85°	2.0
87.5°	2.0
90°	0.0

(END OF REPORT)