

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256050

Luminaire Tested: P3AS02R109040DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1256050  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R109040DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 90CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 185.0 lumens  
Efficiency: N/A  
Efficacy: 48.7 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1256050  
CATALOG NUMBER: P3AS02R109040DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1256050  
 CATALOG NUMBER: P3AS02R109040DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72	72	72	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55	55	55	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	62	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	53833
5°	50473
10°	41393
15°	32145
20°	25389
25°	20227
30°	16230
35°	13251
40°	10906
45°	9179
50°	7880
55°	6843
60°	6052
65°	5241
70°	4680
75°	3813
80°	3031
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9179 cd/sqm



TEST NUMBER: P1256050  
 CATALOG NUMBER: P3AS02R109040DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.5	11.1
10°-20°	39.7	21.4
20°-30°	38.6	20.8
30°-40°	31.2	16.8
40°-50°	23.1	12.5
50°-60°	16.2	8.7
60°-70°	10.1	5.5
70°-80°	4.8	2.6
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.7	53.4
0°-40°	129.9	70.2
0°-60°	169.2	91.5
0°-90°	185.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	185.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	246	
5°	229	20
15°	142	40
25°	84	39
35°	50	31
45°	30	23
55°	18	16
65°	10	10
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1256050  
CATALOG NUMBER: P3AS02R109040DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	245.5
2.5°	241.5
5°	229.3
7.5°	209.8
10°	185.9
12.5°	162.3
15°	141.6
17.5°	124.2
20°	108.8
22.5°	95.4
25°	83.6
27.5°	73.0
30°	64.1
32.5°	56.4
35°	49.5
37.5°	43.4
40°	38.1
42.5°	33.7
45°	29.6
47.5°	26.4
50°	23.1
52.5°	20.3
55°	17.9
57.5°	15.8
60°	13.8
62.5°	11.8
65°	10.1
67.5°	8.5
70°	7.3
72.5°	5.7
75°	4.5
77.5°	3.2
80°	2.4
82.5°	1.2
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)