

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256750

Luminaire Tested: P3AS05R559040DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559040DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 587.0 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256750

CATALOG NUMBER: P3AS05R559040DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1256750

CATALOG NUMBER: P3AS05R559040DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	84		87	85	82
4	97	90	84	80		95	89	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		86	78	73	68		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	70	64	60		69	63	60		67	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	73	63	57	53		72	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161193
5°	159542
10°	154083
15°	142430
20°	122907
25°	97070
30°	68846
35°	44410
40°	26679
45°	15040
50°	8085
55°	2867
60°	2588
65°	2491
70°	2436
75°	2288
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 15040 cd/sqm

TEST NUMBER: P1256750

CATALOG NUMBER: P3AS05R559040DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	11.6
10°-20°	173.5	29.6
20°-30°	181.8	31.0
30°-40°	106.1	18.1
40°-50°	39.7	6.8
50°-60°	9.3	1.6
60°-70°	4.8	0.8
70°-80°	2.8	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.5	72.1
0°-40°	529.5	90.2
0°-60°	578.6	98.6
0°-90°	587.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	735	
5°	725	68
15°	627	173
25°	401	182
35°	166	106
45°	48	40
55°	8	9
65°	5	5
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1256750

CATALOG NUMBER: P3AS05R559040DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	735.1
2.5°	732.9
5°	724.8
7.5°	711.9
10°	692.0
12.5°	664.0
15°	627.4
17.5°	581.1
20°	526.7
22.5°	465.8
25°	401.2
27.5°	335.0
30°	271.9
32.5°	214.9
35°	165.9
37.5°	126.0
40°	93.2
42.5°	66.8
45°	48.5
47.5°	35.0
50°	23.7
52.5°	13.5
55°	7.5
57.5°	6.5
60°	5.9
62.5°	5.4
65°	4.8
67.5°	4.3
70°	3.8
72.5°	3.2
75°	2.7
77.5°	2.2
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)