

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256094

Luminaire Tested: P3AS02R159040DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256094
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159040DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 133.0 lumens
Efficiency: N/A
Efficacy: 36.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256094

CATALOG NUMBER: P3AS02R159040DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256094

CATALOG NUMBER: P3AS02R159040DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113609
5°	100858
10°	70028
15°	41408
20°	23592
25°	13477
30°	7470
35°	3989
40°	2204
45°	1178
50°	751
55°	573
60°	526
65°	467
70°	385
75°	424
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1178 cd/sqm

TEST NUMBER: P1256094

CATALOG NUMBER: P3AS02R159040DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	29.3
10°-20°	51.4	38.7
20°-30°	26.5	19.9
30°-40°	9.9	7.5
40°-50°	3.2	2.4
50°-60°	1.4	1.1
60°-70°	0.9	0.7
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.9	87.9
0°-40°	126.8	95.3
0°-60°	131.4	98.8
0°-90°	133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	458	39
15°	182	51
25°	56	26
35°	15	10
45°	4	3
55°	2	1
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1256094

CATALOG NUMBER: P3AS02R159040DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	518.1
1°	517.1
2°	510.3
3°	497.4
4°	480.3
5°	458.2
6°	433.1
7°	405.5
8°	374.9
9°	344.7
10°	314.5
12.5°	242.0
15°	182.4
17.5°	136.6
20°	101.1
22.5°	75.5
25°	55.7
27.5°	40.6
30°	29.5
32.5°	20.9
35°	14.9
37.5°	10.6
40°	7.7
42.5°	5.5
45°	3.8
47.5°	2.8
50°	2.2
52.5°	1.8
55°	1.5
57.5°	1.3
60°	1.2
62.5°	1.0
65°	0.9
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.3
85°	0.1
87.5°	0.0
90°	0.0

(END OF REPORT)