

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256761

Luminaire Tested: P3AS05R609040DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609040DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 645.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256761
CATALOG NUMBER: P3AS05R609040DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1256761
 CATALOG NUMBER: P3AS05R609040DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169000
5°	159542
10°	155397
15°	151851
20°	141179
25°	126201
30°	96395
35°	55653
40°	21612
45°	8993
50°	1979
55°	306
60°	219
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8993 cd/sqm



TEST NUMBER: P1256761
 CATALOG NUMBER: P3AS05R609040DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.4	10.6
10°-20°	186.3	28.9
20°-30°	233.3	36.2
30°-40°	130.5	20.2
40°-50°	24.8	3.8
50°-60°	1.3	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.1	75.7
0°-40°	618.5	95.9
0°-60°	644.6	99.9
0°-90°	645.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	771	
5°	725	68
15°	669	186
25°	522	233
35°	208	130
45°	29	25
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1256761
CATALOG NUMBER: P3AS05R609040DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	770.7
1°	767.5
2°	757.5
3°	745.6
4°	734.6
5°	724.8
6°	717.4
7°	711.1
8°	706.3
9°	701.8
10°	697.9
11°	693.9
12°	689.4
13°	683.9
14°	677.3
15°	668.9
16°	658.6
17°	647.0
18°	633.8
19°	618.7
20°	605.0
21°	590.2
22°	574.9
23°	558.8
24°	541.2
25°	521.6
26°	498.7
27°	473.1
28°	444.3
29°	413.7
30°	380.7
31°	347.5
32°	313.2
32.5°	294.5
33°	277.6
34°	242.5
35°	207.9
36°	176.8
37°	143.8
37.5°	128.8
38°	114.0
39°	91.8
40°	75.5
42.5°	45.9
45°	29.0



TEST NUMBER: P1256761
CATALOG NUMBER: P3AS05R609040DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	16.1
50°	5.8
52.5°	1.3
55°	0.8
57.5°	0.5
60°	0.5
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)