

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256832

Luminaire Tested: P3AS05R709040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256832
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 387.0 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256832

CATALOG NUMBER: P3AS05R709040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256832

CATALOG NUMBER: P3AS05R709040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90782
5°	89104
10°	84033
15°	76255
20°	66692
25°	56277
30°	46083
35°	35737
40°	25591
45°	16188
50°	8085
55°	4932
60°	4254
65°	3891
70°	3462
75°	3219
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16188 cd/sqm

TEST NUMBER: P1256832

CATALOG NUMBER: P3AS05R709040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.8	9.8
10°-20°	93.5	24.2
20°-30°	106.5	27.5
30°-40°	83.2	21.5
40°-50°	40.9	10.6
50°-60°	12.6	3.2
60°-70°	7.5	1.9
70°-80°	4.0	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.7	61.4
0°-40°	320.9	82.9
0°-60°	374.4	96.7
0°-90°	387.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	387.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	405	38
15°	336	93
25°	233	106
35°	134	83
45°	52	41
55°	13	13
65°	8	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1256832

CATALOG NUMBER: P3AS05R709040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.0
2.5°	411.8
5°	404.8
7.5°	393.5
10°	377.4
12.5°	358.5
15°	335.9
17.5°	311.7
20°	285.8
22.5°	258.9
25°	232.6
27.5°	206.7
30°	182.0
32.5°	157.2
35°	133.5
37.5°	110.9
40°	89.4
42.5°	69.4
45°	52.2
47.5°	36.6
50°	23.7
52.5°	15.6
55°	12.9
57.5°	11.3
60°	9.7
62.5°	8.6
65°	7.5
67.5°	6.5
70°	5.4
72.5°	4.3
75°	3.8
77.5°	3.2
80°	2.2
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)