

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256186

Luminaire Tested: P3AS02R309040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 278.1 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256186

CATALOG NUMBER: P3AS02R309040DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1256186

CATALOG NUMBER: P3AS02R309040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	85	81	77		84	80	77		83	79	76		81	78	76
7	90	82	77	74		89	82	77	74		81	76	73		80	76	73		78	75	73
8	87	79	74	71		86	79	74	71		78	73	70		77	73	70		76	72	70
9	84	76	71	68		83	75	71	68		75	70	67		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	67	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162224
5°	154391
10°	129880
15°	93667
20°	58105
25°	33050
30°	18357
35°	9985
40°	5267
45°	2853
50°	1535
55°	994
60°	921
65°	934
70°	833
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2853 cd/sqm

TEST NUMBER: P1256186

CATALOG NUMBER: P3AS02R309040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	22.7
10°-20°	112.3	40.4
20°-30°	64.9	23.3
30°-40°	24.6	8.9
40°-50°	7.6	2.7
50°-60°	2.6	0.9
60°-70°	1.7	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	240.3	86.4
0°-40°	265.0	95.3
0°-60°	275.1	98.9
0°-90°	278.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	740	
5°	701	63
15°	413	112
25°	137	65
35°	37	25
45°	9	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1256186

CATALOG NUMBER: P3AS02R309040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	739.8
1°	739.3
2°	734.8
3°	726.4
4°	715.9
5°	701.4
6°	683.1
7°	662.6
8°	639.7
9°	612.4
10°	583.3
11°	551.8
12°	518.4
13°	483.5
14°	448.0
15°	412.6
17.5°	325.4
20°	249.0
22.5°	184.6
25°	136.6
27.5°	99.3
30°	72.5
32.5°	52.3
35°	37.3
37.5°	26.0
40°	18.4
42.5°	12.9
45°	9.2
47.5°	6.3
50°	4.5
52.5°	3.2
55°	2.6
57.5°	2.4
60°	2.1
62.5°	1.8
65°	1.8
67.5°	1.6
70°	1.3
72.5°	1.1
75°	0.8
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.0



TEST NUMBER: P1256186
CATALOG NUMBER: P3AS02R309040DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)