

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256201

Luminaire Tested: P3AS02R309040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 169.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256201

CATALOG NUMBER: P3AS02R309040DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256201

CATALOG NUMBER: P3AS02R309040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		68	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57759
5°	55954
10°	50411
15°	41703
20°	32296
25°	24219
30°	17572
35°	11725
40°	7214
45°	4217
50°	2593
55°	2103
60°	1842
65°	1505
70°	1346
75°	1356
80°	1010
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4217 cd/sqm

TEST NUMBER: P1256201

CATALOG NUMBER: P3AS02R309040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.4	13.8
10°-20°	50.6	29.9
20°-30°	46.0	27.2
30°-40°	27.8	16.5
40°-50°	11.1	6.6
50°-60°	4.9	2.9
60°-70°	3.0	1.8
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.0	71.0
0°-40°	147.8	87.5
0°-60°	163.9	97.0
0°-90°	169.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	169.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	263	
5°	254	23
15°	184	51
25°	100	46
35°	44	28
45°	14	11
55°	6	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1256201

CATALOG NUMBER: P3AS02R309040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	263.4
1°	263.1
2°	262.1
3°	260.2
4°	257.6
5°	254.2
6°	250.0
7°	245.5
8°	239.8
9°	233.2
10°	226.4
11°	218.6
12°	210.2
13°	201.8
14°	192.6
15°	183.7
17.5°	160.4
20°	138.4
22.5°	117.9
25°	100.1
27.5°	83.9
30°	69.4
32.5°	56.1
35°	43.8
37.5°	33.5
40°	25.2
42.5°	18.3
45°	13.6
47.5°	10.2
50°	7.6
52.5°	6.0
55°	5.5
57.5°	4.7
60°	4.2
62.5°	3.4
65°	2.9
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.3
80°	0.8
82.5°	0.5
85°	0.5
87.5°	0.3



TEST NUMBER: P1256201

CATALOG NUMBER: P3AS02R309040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)