

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256862

Luminaire Tested: P3AS09R109040DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R109040DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 4000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 379.0 lumens
Efficiency: N/A
Efficacy: 30.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256862

CATALOG NUMBER: P3AS09R109040DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1256862

CATALOG NUMBER: P3AS09R109040DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163430
5°	151045
10°	120595
15°	91102
20°	69376
25°	52866
30°	37879
35°	24708
40°	15143
45°	9148
50°	6072
55°	4702
60°	4035
65°	3528
70°	3142
75°	3135
80°	2273
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9148 cd/sqm

TEST NUMBER: P1256862

CATALOG NUMBER: P3AS09R109040DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.8	16.0
10°-20°	112.2	29.6
20°-30°	99.9	26.3
30°-40°	59.1	15.6
40°-50°	24.2	6.4
50°-60°	11.4	3.0
60°-70°	6.9	1.8
70°-80°	3.7	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.8	72.0
0°-40°	331.9	87.6
0°-60°	367.5	97.0
0°-90°	379.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	379.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	745	
5°	686	61
15°	401	112
25°	218	100
35°	92	59
45°	30	24
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1256862

CATALOG NUMBER: P3AS09R109040DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	745.3
1°	743.5
2°	737.9
3°	726.9
4°	708.4
5°	686.2
6°	662.2
7°	633.9
8°	604.4
9°	574.2
10°	541.6
12.5°	467.1
15°	401.3
17.5°	344.7
20°	297.3
22.5°	255.4
25°	218.5
27.5°	182.8
30°	149.6
32.5°	119.4
35°	92.3
37.5°	70.8
40°	52.9
42.5°	39.4
45°	29.5
47.5°	22.8
50°	17.8
52.5°	14.8
55°	12.3
57.5°	10.5
60°	9.2
62.5°	8.0
65°	6.8
67.5°	6.2
70°	4.9
72.5°	4.3
75°	3.7
77.5°	2.5
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)