

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256223

Luminaire Tested: P3AS02R359040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 212.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256223

CATALOG NUMBER: P3AS02R359040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256223

CATALOG NUMBER: P3AS02R359040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48417
5°	47391
10°	44399
15°	39841
20°	34653
25°	29542
30°	24738
35°	19702
40°	14255
45°	9024
50°	4912
55°	3403
60°	3201
65°	3009
70°	2885
75°	2457
80°	2273
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9024 cd/sqm

TEST NUMBER: P1256223

CATALOG NUMBER: P3AS02R359040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.0	9.5
10°-20°	48.8	23.0
20°-30°	56.0	26.4
30°-40°	45.7	21.5
40°-50°	23.1	10.9
50°-60°	8.5	4.0
60°-70°	5.7	2.7
70°-80°	3.2	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	124.9	58.9
0°-40°	170.6	80.4
0°-60°	202.2	95.3
0°-90°	212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	221	
5°	215	20
15°	176	49
25°	122	56
35°	74	46
45°	29	23
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256223

CATALOG NUMBER: P3AS02R359040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	220.8
1°	220.6
2°	220.1
3°	219.0
4°	217.4
5°	215.3
6°	212.7
7°	210.1
8°	206.7
9°	203.3
10°	199.4
11°	195.2
12°	190.7
13°	185.7
14°	180.5
15°	175.5
17.5°	162.2
20°	148.5
22.5°	134.7
25°	122.1
27.5°	109.8
30°	97.7
32.5°	85.7
35°	73.6
37.5°	61.6
40°	49.8
42.5°	38.8
45°	29.1
47.5°	21.0
50°	14.4
52.5°	10.5
55°	8.9
57.5°	8.1
60°	7.3
62.5°	6.5
65°	5.8
67.5°	5.0
70°	4.5
72.5°	3.7
75°	2.9
77.5°	2.4
80°	1.8
82.5°	1.3
85°	0.8
87.5°	0.5



TEST NUMBER: P1256223

CATALOG NUMBER: P3AS02R359040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)