

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256889

Luminaire Tested: P3AS09R159040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R159040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 238.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256889

CATALOG NUMBER: P3AS09R159040DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1256889

CATALOG NUMBER: P3AS09R159040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102623
5°	94849
10°	75728
15°	57208
20°	43567
25°	33195
30°	23776
35°	15526
40°	9504
45°	5768
50°	3821
55°	2944
60°	2544
65°	2231
70°	1988
75°	1949
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5768 cd/sqm

TEST NUMBER: P1256889

CATALOG NUMBER: P3AS09R159040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.2	16.0
10°-20°	70.4	29.6
20°-30°	62.7	26.3
30°-40°	37.1	15.6
40°-50°	15.2	6.4
50°-60°	7.2	3.0
60°-70°	4.4	1.8
70°-80°	2.3	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.3	72.0
0°-40°	208.4	87.6
0°-60°	230.8	97.0
0°-90°	238.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	238.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	468	
5°	431	38
15°	252	70
25°	137	63
35°	58	37
45°	19	15
55°	8	7
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1256889

CATALOG NUMBER: P3AS09R159040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	468.0
1°	466.9
2°	463.4
3°	456.4
4°	444.8
5°	430.9
6°	415.9
7°	398.1
8°	379.5
9°	360.6
10°	340.1
12.5°	293.3
15°	252.0
17.5°	216.4
20°	186.7
22.5°	160.4
25°	137.2
27.5°	114.8
30°	93.9
32.5°	75.0
35°	58.0
37.5°	44.4
40°	33.2
42.5°	24.7
45°	18.6
47.5°	14.3
50°	11.2
52.5°	9.3
55°	7.7
57.5°	6.6
60°	5.8
62.5°	5.0
65°	4.3
67.5°	3.9
70°	3.1
72.5°	2.7
75°	2.3
77.5°	1.5
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)