

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256256

Luminaire Tested: P3AS02R409040DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409040DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 94.0 lumens
Efficiency: N/A
Efficacy: 26.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256256
CATALOG NUMBER: P3AS02R409040DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1256256
 CATALOG NUMBER: P3AS02R409040DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29274
5°	28681
10°	26697
15°	23269
20°	18762
25°	14057
30°	9875
35°	6478
40°	3922
45°	2357
50°	1399
55°	1109
60°	1009
65°	882
70°	833
75°	678
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2357 cd/sqm



TEST NUMBER: P1256256
 CATALOG NUMBER: P3AS02R409040DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.1	12.9
10°-20°	28.2	30.0
20°-30°	26.6	28.3
30°-40°	15.4	16.4
40°-50°	6.1	6.5
50°-60°	2.7	2.9
60°-70°	1.7	1.8
70°-80°	0.9	0.9
80°-90°	0.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	66.9	71.2
0°-40°	82.3	87.6
0°-60°	91.2	97.0
0°-90°	94.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	94.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	134	
5°	130	12
15°	102	28
25°	58	27
35°	24	15
45°	8	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1256256
CATALOG NUMBER: P3AS02R409040DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	133.5
2.5°	132.7
5°	130.3
7.5°	125.8
10°	119.9
12.5°	112.0
15°	102.5
17.5°	91.9
20°	80.4
22.5°	68.9
25°	58.1
27.5°	48.1
30°	39.0
32.5°	31.1
35°	24.2
37.5°	18.3
40°	13.7
42.5°	10.2
45°	7.6
47.5°	5.5
50°	4.1
52.5°	3.3
55°	2.9
57.5°	2.7
60°	2.3
62.5°	1.9
65°	1.7
67.5°	1.4
70°	1.3
72.5°	1.0
75°	0.8
77.5°	0.6
80°	0.5
82.5°	0.4
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)