

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256911

Luminaire Tested: P3AS09R209040DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256911
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209040DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 815.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256911
CATALOG NUMBER: P3AS09R209040DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1256911
 CATALOG NUMBER: P3AS09R209040DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	627055
5°	569996
10°	421257
15°	260592
20°	148810
25°	84948
30°	47653
35°	25913
40°	14198
45°	7815
50°	4571
55°	3326
60°	3114
65°	2854
70°	2500
75°	2626
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7815 cd/sqm



TEST NUMBER: P1256911
 CATALOG NUMBER: P3AS09R209040DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.2	27.5
10°-20°	320.1	39.3
20°-30°	167.1	20.5
30°-40°	64.6	7.9
40°-50°	21.0	2.6
50°-60°	8.3	1.0
60°-70°	5.4	0.7
70°-80°	3.2	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.4	87.3
0°-40°	776.0	95.2
0°-60°	805.3	98.8
0°-90°	815.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	815.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2860	
5°	2590	224
15°	1148	320
25°	351	167
35°	97	65
45°	25	21
55°	9	8
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1256911
CATALOG NUMBER: P3AS09R209040DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2859.6
1°	2854.1
2°	2820.2
3°	2768.2
4°	2687.9
5°	2589.5
6°	2473.0
7°	2343.9
8°	2194.3
9°	2048.6
10°	1891.9
12.5°	1503.8
15°	1147.9
17.5°	859.0
20°	637.7
22.5°	472.4
25°	351.1
27.5°	259.0
30°	188.2
32.5°	136.2
35°	96.8
37.5°	70.1
40°	49.6
42.5°	35.4
45°	25.2
47.5°	18.1
50°	13.4
52.5°	10.2
55°	8.7
57.5°	7.9
60°	7.1
62.5°	6.3
65°	5.5
67.5°	4.7
70°	3.9
72.5°	3.9
75°	3.1
77.5°	2.4
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)