

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256280

Luminaire Tested: P3AS02R459040DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459040DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 4000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256280

CATALOG NUMBER: P3AS02R459040DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1256280

CATALOG NUMBER: P3AS02R459040DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	90	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48132
5°	47281
10°	44733
15°	40795
20°	36076
25°	31332
30°	26890
35°	22406
40°	16688
45°	10234
50°	4742
55°	3708
60°	3552
65°	3269
70°	3013
75°	2881
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10234 cd/sqm

TEST NUMBER: P1256280

CATALOG NUMBER: P3AS02R459040DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.1	8.8
10°-20°	50.0	22.0
20°-30°	59.4	26.2
30°-40°	51.6	22.8
40°-50°	25.9	11.4
50°-60°	9.0	4.0
60°-70°	6.3	2.8
70°-80°	3.5	1.5
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.6	57.1
0°-40°	181.2	79.8
0°-60°	216.1	95.2
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	220	
5°	215	20
15°	180	50
25°	130	59
35°	84	52
45°	33	26
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1256280

CATALOG NUMBER: P3AS02R459040DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	219.5
2.5°	218.4
5°	214.8
7.5°	209.0
10°	200.9
12.5°	191.0
15°	179.7
17.5°	167.2
20°	154.6
22.5°	141.8
25°	129.5
27.5°	117.7
30°	106.2
32.5°	95.2
35°	83.7
37.5°	71.4
40°	58.3
42.5°	45.5
45°	33.0
47.5°	21.7
50°	13.9
52.5°	10.7
55°	9.7
57.5°	8.9
60°	8.1
62.5°	7.3
65°	6.3
67.5°	5.5
70°	4.7
72.5°	3.9
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.6
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)