

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256337

Luminaire Tested: P3AS02R559040DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1256337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559040DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 4000K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 222.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1256337

CATALOG NUMBER: P3AS02R559040DE010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1256337

CATALOG NUMBER: P3AS02R559040DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	96		95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41751
5°	41206
10°	39590
15°	37026
20°	33766
25°	30123
30°	26358
35°	21897
40°	17261
45°	11722
50°	7164
55°	3708
60°	3465
65°	3269
70°	3013
75°	2626
80°	2652
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11722 cd/sqm

TEST NUMBER: P1256337

CATALOG NUMBER: P3AS02R559040DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.6	7.9
10°-20°	45.6	20.5
20°-30°	57.1	25.7
30°-40°	51.0	23.0
40°-50°	29.8	13.4
50°-60°	10.3	4.6
60°-70°	6.2	2.8
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.2	54.2
0°-40°	171.2	77.1
0°-60°	211.3	95.2
0°-90°	222.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	222.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	190	
5°	187	18
15°	163	46
25°	124	57
35°	82	51
45°	38	30
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1256337

CATALOG NUMBER: P3AS02R559040DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	190.4
2.5°	189.3
5°	187.2
7.5°	183.0
10°	177.8
12.5°	171.2
15°	163.1
17.5°	154.4
20°	144.7
22.5°	134.8
25°	124.5
27.5°	114.3
30°	104.1
32.5°	93.1
35°	81.8
37.5°	70.8
40°	60.3
42.5°	49.0
45°	37.8
47.5°	28.8
50°	21.0
52.5°	13.6
55°	9.7
57.5°	8.7
60°	7.9
62.5°	7.1
65°	6.3
67.5°	5.5
70°	4.7
72.5°	3.9
75°	3.1
77.5°	2.6
80°	2.1
82.5°	1.3
85°	0.8
87.5°	0.5
90°	0.0

(END OF REPORT)