

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1256351

Luminaire Tested: P3AS02R609040DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1256351  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R609040DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 4000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 313.9 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1256351  
CATALOG NUMBER: P3AS02R609040DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1256351  
 CATALOG NUMBER: P3AS02R609040DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	82274
5°	77658
10°	75639
15°	73916
20°	68723
25°	61431
30°	46919
35°	27090
40°	10505
45°	4373
50°	955
55°	153
60°	132
65°	52
70°	64
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4373 cd/sqm



TEST NUMBER: P1256351  
 CATALOG NUMBER: P3AS02R609040DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.3	10.6
10°-20°	90.7	28.9
20°-30°	113.6	36.2
30°-40°	63.5	20.2
40°-50°	12.0	3.8
50°-60°	0.6	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.6	75.7
0°-40°	301.1	95.9
0°-60°	313.8	99.9
0°-90°	313.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	313.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	375	
5°	353	33
15°	326	91
25°	254	114
35°	101	64
45°	14	12
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1256351  
CATALOG NUMBER: P3AS02R609040DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	375.2
1°	373.7
2°	368.8
3°	363.0
4°	357.6
5°	352.8
6°	349.2
7°	346.2
8°	343.9
9°	341.7
10°	339.7
11°	337.8
12°	335.6
13°	332.9
14°	329.7
15°	325.6
16°	320.6
17°	315.0
18°	308.5
19°	301.2
20°	294.5
21°	287.3
22°	279.9
23°	272.0
24°	263.4
25°	253.9
26°	242.8
27°	230.3
28°	216.3
29°	201.4
30°	185.3
31°	169.2
32°	152.5
32.5°	143.3
33°	135.1
34°	118.0
35°	101.2
36°	86.1
37°	70.0
37.5°	62.7
38°	55.5
39°	44.7
40°	36.7
42.5°	22.3
45°	14.1



TEST NUMBER: P1256351  
CATALOG NUMBER: P3AS02R609040DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	7.8
50°	2.8
52.5°	0.6
55°	0.4
57.5°	0.3
60°	0.3
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)